AIRSENSE ANALYTICS



GDA-FR Gas Detector Array - First Response

Portable detector for hazardous gases and chemicals


The portable Gas Detector Array is a battery operated analytical instrument specifically designed to measure and monitor most common gases. This instrument is used by Police, Fire Departments and many different operators from public security.

The GDA has been designed for the detection and identification of Toxic Industrial Compounds (TICs) and Chemical Warfare Agents (CWAs) – with optional expansion to the range of the most common explosives.

With its Hybrid Sensor Array it alerts to a wide range of hazardous gases. It offers high level safety without the need to select the "right" detector.

Alarms are released as soon as gases appear in dangerous concentrations – whether it is ppb or ppm range. Compounds matching with the adaptable libraries are displayed automatically in the display. The GDA is always available. A specialized gas-flow control allows faster deployment and the unit retains its sensitivity and reliability.







defense



The GDA set allows

- High security through a wide coverage of a variety of gases and chemicals at a low concentration level
- Security and surveillance, public or highlevel political events
- Risk monitoring of jobs chemical manufacturing shear

Advantages

- Increased selectivity
- Portable instrument with integrated display, visual and audible alarm
- High level of safety through broad detection range for hazardous gases
- Detection and identification in seconds
- Works with computer or in standalone
- Substance identification possible using methods of pattern recognition
- Provides reliable results with easy operation even for inexperienced operators or rare
- Data logger and offline data analysis



GDA-FR

Gas Detector Array - First Response

Hazardous compounds / GDA-Mode List with tolerable concentrations*

Substance	Concentration limit* [ppm]	Sensor type
Acetic acid	20	IMS, SC
Acetone	500	IMS, PID, SC
Acroleine	0.2	SC
Acrylonitrile	20	MS, SC
Ammonia	50	IMS, SC, EC
Benzene	20	PID, SC
Carbon dioxide	10000	_
Carbon disulfide	10	IMS
Carbon monoxide	100	SC
Chlorine	1	IMS, EC
Chlorobenzene	100	PID, SC
Chlorocyane	0.3	IMS
Hydrazine	1	IMS
Ethanol	3000	IMS, PID, SC
Formaldehyde	1	SC
Hexane, n-	200	PID, SC
Hydrogen chloride	5	IMS, EC
Hydrogen cyanide	5	IMS, EC
Hydrogen fluoride	5	(IMS), EC
Hydrogen sulfide	10	IMS, EC
Methanol	500	IMS, SC
Nitrogen dioxide	1	IMS
Phosgene	0.1	EC
Phosphine	0.5	EC
Styrene	40	IMS, PID, SC
Sulfur dioxide	1	IMS, EC
Tetrachloroethylene	100	IMS, SC
Toluene	100	PID, SC
Toluene diisocyanate	0.02	IMS
Trichloroethane, 1,1,1-	300	IMS
Trichloroethane, 1,1,2-	25	IMS
Trichloroethylene	100	IMS, PID
Vinyl chloride	100	PID, SC, EC

* Selection of chemical compounds (comparable to ERPG), tolerable concentration values for firefighter working 4 hours without breath protection

Chemical Warfare Agents (IMS-Mode)

Nerves GA (Tabun)	Skin HD (S-Lost)	Blood AC	
GB (Sarin) GD (Soman) GF	HN (N-Lost) L (Lewisit)		
VX			

Technical Data

Modes of Operation:

- GDA mode for hazardous compounds
- IMS mode for chemical warfare agents

Detectors:

- ion mobility spectrometer (Ni63 ion source, positive and negative mode)
- photo ionization detector (10.6 eV)
- electrochemical cell
- 2 metal oxide sensors

Sampling System:

- internal pumps
- internal sample dilution system

Measurement Time:

- typical some seconds to less than 1 minute Identification:
- different pattern recognition methods available Display:
- graphical display integrated

Power:

• 30W, powered by rechargeable battery and/or power supply (serial port – RS-232)

Weight:

• 4.2 kg (8.4 lbm) (without batteries)

Dimensions:

• ca. 395 x 112 x 210 mm (ca. 15.7 x 4.5 x 8.4 in)

Options:

• Infrared heater for thermal desorption and analysis of surfaces